

# MOVING FILTER HEAD FOR ALPHA / BETA-GAMMA AIR CAM

Model ~ MFH-ABG ~ Model ~ MFH-ABG-R

## FEATURES

- MOVING FILTER TAPE
- DETECTS ALPHA, BETA, GAMMA
- **OPTIONAL RADON CHANNEL – MFH-ABG-R**
- AUTOMATIC ADVANCE
- REMOTE AIR SAMPLING DETECTOR HEAD
- OPEN FACE BREATHING ZONE OPERATION FOR ROOM AIR
- SEALED PLASTIC CASE WITH CARRYING HANDLE
- CLEAR FRONT PANEL
- USE WITH WIDE VARIETY OF:  
DETECTORS & ELECTRONICS



## DESCRIPTION:

### FILTER TAPE:

- MATERIAL: 5.0 um TEFLON MEMBRANE FILTER
- SPECLON# BSP-FILT-50BTA
- WIDTH: 1.25"
- LENGTH: 1,200" (other lengths optional)

### OPERATION:

- 1 YEAR 1 YEAR UNATTENDED USE – STEP EVERY 8 HRS
- 1 MONTH 1 MONTH UNATTENDED USE – STEP EVERY 1 HR

### WEIGHT & DIMENSIONS:

- SIZE : 5" X 10" X 7" WEIGHT: 5 LBS

### MODES OF OPERATION:(User Specified)

- **REMOTE START:** SINGLE SHOT
- **TIMED OPERATION:** -- (PRESET TIME)
  - SINGLE SHOT - AUTO REPEAT

### OPTIONS & ACCESSORIES:

- FILTER ROLLS- LONGER, SHORTER
- FLOW RATE 3 LPM STANDARD, OTHER FLOW RATES AVAILABLE
- SNIFFER HOSE HOOD, GLOVE-BOX, STACK OR OTHER LOCATION
- MASS FLOW SENSOR PRECISION HOTWIRE SENSOR OR SIMPLE ROTOMETER
- POWER 115 VAC – 60HZ STANDARD; 230 VAC – 50 HZ; **OPTIONAL DC**
- MOUNTING WALL MOUNT, HANDHELD, OR TRIPOD



**TECHNICAL ASSOCIATES**

7051 ETON AVENUE, CANOGA PARK, CALIFORNIA 91303

PHONE: 818-883-7043 | FAX: 818-883-6103

SALES@TECH-ASSOCIATES.COM | TECH-ASSOCIATES.COM | USNUCLEARCORP.COM

DIVISION OF




USNUCLEARCORP

OTCOB-UCLC

# MOVING FILTER HEAD FOR ALPHA / BETA-GAMMA AIR CAM

Model ~ MFH-ABG ~ Model ~ MFH-ABG-R



MOVING AIR FILTER FLOW DIAGRAM



**TECHNICAL ASSOCIATES**

7051 ETON AVENUE, CANOGA PARK, CALIFORNIA 91303

PHONE: 818-883-7043 | FAX: 818-883-6103

SALES@TECH-ASSOCIATES.COM | TECH-ASSOCIATES.COM | USNUCLEARCORP.COM

DIVISION OF



USNUCLEARCORP

OTCOB-UCLC