FLOOR MONITORS ALPHA plus BETA-GAMMA

Model Series ~ ABFM SERIES


Model ~ ABFM-5 Pancake Array GM Model ~ ABFM-6 Scintillator Model ~ ABFM-7 Gas Flow

FEATURES:

- ABFM-5 DETECTS ALPHA, BETA, GAMMA **TOGETHER**
- **ABFM-5 12 LARGE WINDOW GM PANCAKE DETECTORS**
- **ABFM-6 DUAL DETECTORS** ZnS(Ag) for Alpha Beta Scintillator Sheet
- ABFM-7 GAS FLOW PROPORTIONAL DUAL **DETECTOR**
- LARGE FACE 144 square inches (925 cm) on ABFM-6 and ABFM-7
- PRS-2S ELECTRONICS SEPARATES ALPHA FROM BETA-GAMMA IN ABFM-6 AND ABFM-7
- FAST AND SENSITIVE
- DIGITAL READOUT
- **OUTPUT FOR RECORDER**
- RUGGED, EASY DECONTAMINATION
- **BUILT-IN SPEAKER**



ABFM-SERIES FLOOR MONITORS



ABFM-SERIES FLOOR MONITORS **INTERIOR**



PRS-2S **ELECTRONICS**

DESCRIPTION:

Alpha plus Beta Gamma Floor Monitors, Models ABFM-5, 6, & 7 utilize Alpha-Beta-Gamma sensitive detectors coupled to Model PRS-2 electronics with backlight.

- An electronic sorter accepts and displays Alpha counts only or Alphas plus Beta-Gamma, or Beta-Gamma only.
- Windows are protected by a frame and grid which is easily removed for decontamination.
- The very large face detectors achieve the fastest most sensitive floor monitoring system currently available.





TECHNICAL ASSOCIATES OVERHOFF TECHNOLOGY





OTCQB - UCLE

FLOOR MONITORS ALPHA plus BETA-GAMMA

Model Series ~ ABFM SERIES

Model ~ ABFM-5 Pancake Array GM Model ~ ABFM-6 Scintillator Model ~ ABFM-7 Gas Flow

SPECIFICATIONS:

PRS-2S ELECTRONICS:

- PORTABLE OR BENCH TOP
- **DUAL DIGITAL DISPLAY BATTERY OPERATION**
- 2 SEPARATE SCALE FACTORS FOR RATE & TOTAL
- 0.1-99 sec TIME CONSTANT FOR RATEMETER
- 8 DIGIT LCD DISPLAY
- ALARM AUDIO/VISUAL
- BRING YOUR OWN STOP WATCH, IDEAL FOR LONG COUNT UP TO 24 HOURS OR MORE
- ANY GM OR SCINTILLATION ALPHA, BETA, GAMMA, X-RAY, POSITRON DETECTOR.
- **USB OPTIONAL: RS-232 SERIAL PORT**
- **OPTIONAL: PRE-AMPLIFIER**
- **CE MARK**
- IP64
- Reads out from 2 separate probes simultaneously No energy discrimination

Alarm: Audio / Visual, Low Battery Warning

-10 C° to 40° C Temperature:

Power: Batteries: 6 AA cells or optional in-place rechargeable batteries. **Battery Life:** 100 hours with Alkaline cells (200 hours with - Lithium cells).

Construction: All plug in circuit cards, essentially no wires. Rugged, lightweight **Dimensions:** 3-1/4" H, 4-1/4 W, 7-1/4" long excluding probe holder and handle.

Weight: 2 lbs.

Options: RS-232 serial port

Pre-amp for proportional detectors

Other connectors - MHV etc In-place rechargeable batteries







FLOOR MONITORS ALPHA plus BETA-GAMMA

Model Series ~ ABFM SERIES

Model ~ ABFM-5 Pancake Array GM Model ~ ABFM-6 Scintillator

Model ~ ABFM-7 Gas Flow

MODELS:

ABFM-5: 12 large window, GM pancake detectors, 29 sq. inches coverage in 24 inch swath.

Window 1.5-2 mg/cm.

Sees Alpha plus all common Betas except H-3.

Physical Features:

Adjustable height above floor.

Adjustable handle, minimum 43" (110 cm) height

Weight 4 kg

The ABFM-5 sees all Alpha, Beta and Gamma together. It does not sort.

PRS-2S Electronics:

See PRS-2S details

ABFM-6: **Detector Details:**

> 4 PM tubes collect information from 144 sq. inches (925 cm) of ZnS(Ag) protected by thin light-tight easily replaceable window plus grille.

6" x 24" detector face; Window is less than 1 mg/cm.

Detector Types: ZnS(Ag) for Alpha

Beta Scintillator Sheet located behind the Alpha detector

PRS-2S Electronics:

Alpha only or Beta-Gamma only or all.

Digital readout.

Power: Lithium Ion Battery Pack

Physical Features:

Adjustable height above floor.

Convenient handle

Weight 8 pounds (4 kg)

Three ball bearing wheels including swivel rear wheel for pivot ease

144 sq. inches thin window gas flow proportional dual detector.

Window is less than 1 mg/cm.

PRS-2S Electronics:

Sees Alphas and all common Betas except H-3.

Sees X-rays (eg Gammas down to 5 KeV but with less efficiency.

Switch selectable for Alpha or Beta-Gamma or all.

Pulse height analyzer; Analog plus digital response.

Physical Features:

Adjustable height above floor.

Output for recorder; Includes gas supply (P-10).



ABFM-7:



